

# Spiral plastic tubing PUN-10X1,5-S-6-BL

Part number: 197598

**FESTO**



## Data sheet

| Feature                                  | Value                                                             |
|------------------------------------------|-------------------------------------------------------------------|
| Working length                           | 6 m                                                               |
| Outside diameter                         | 10 mm                                                             |
| Block length                             | 0.91 m                                                            |
| Inside diameter                          | 7 mm                                                              |
| Winding diameter                         | 80 mm                                                             |
| Number of turns                          | 70                                                                |
| Temperature-dependent operating pressure | -0.095 MPa...1 MPa<br>-0.95 bar...10 bar<br>-13.775 psi...145 psi |
| Approval                                 | German Technical Control Board (TÜV)                              |
| Certificate issuing authority            | B 013277 0506 00                                                  |
| Operating medium                         | Compressed air to ISO 8573-1:2010 [7:-:-]                         |
| LABS (PWIS) conformity                   | VDMA24364-B2-L                                                    |
| Ambient temperature                      | -35 °C...60 °C                                                    |
| Product weight                           | 760 g                                                             |
| Pneumatic connection                     | For push-in connector O.D. 10 mm                                  |
| Colour                                   | Blue                                                              |
| Shore hardness                           | D 52 +/-3                                                         |
| Material tubing                          | TPE-U(PU)                                                         |