

Spiral plastic tubing PUN-4X0,75-S-1,5-SW

Part number: 197604

FESTO



Data sheet

Feature	Value
Working length	1.5 m
Outside diameter	4 mm
Block length	0.384 m
Inside diameter	2.6 mm
Winding diameter	25 mm
Number of turns	70
Temperature-dependent operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C...60 °C
Product weight	42 g
Pneumatic connection	For push-in connector O.D. 4 mm For barbed fitting I.D. 3 mm with union nut For barbed fitting I.D. 3 mm
Colour	Black
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)