

Spiral plastic tubing PUN-8X1,25-S-2-SW

Part number: 197609

FESTO



Data sheet

Feature	Value
Working length	2 m
Outside diameter	8 mm
Block length	0.424 m
Inside diameter	5.7 mm
Winding diameter	60 mm
Number of turns	27
Temperature-dependent operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C...60 °C
Product weight	140 g
Pneumatic connection	For push-in connector O.D. 8 mm For barbed fitting inside diameter of 6 mm with union nut For barbed fitting inside diameter of 6 mm
Colour	Black
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)