

# Spiral plastic tubing PPS-6-15-1/4-BL

Part number: 19797

**FESTO**



## Data sheet

Feature	Value
Working length	15 m
Outside diameter	7.8 mm
Block length	0.8 m
Inside diameter	6.2 mm
Winding diameter	75 mm
Number of turns	86
Temperature-dependent operating pressure	-0.95 bar...17.2 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C...80 °C
Nominal torque	11 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	500 g
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	Male thread G1/4
Colour	Blue
Material connecting thread	Brass
Note on materials	RoHS-compliant
Material buckling protection	Steel Galvanised
Material tubing	PA12-P