

Union nut MCK-PK-13

Part number: 206504

FESTO



Data sheet

Feature	Value
Size	Female thread M22x1
Operating pressure complete temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Pneumatic connection, port 1	For barbed connector I.D. 13 mm with union nut
Material union nut	Wrought aluminium alloy, anodised
Note on materials	RoHS-compliant