

Union nut
MCK-PK-6-KU
Part number: 211292

FESTO



Data sheet

Feature	Value
Size	Female thread M12x1
Operating pressure complete temperature range	0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Pneumatic connection, port 1	For tubing outer diameter of 8 mm For barbed fitting I.D. 6 mm with union nut
Material union nut	POM
Note on materials	RoHS-compliant