

metal braided hose


P-9-BL

Part number: 2232

Product to be discontinued

FESTO

Type to be discontinued. Available until 2018. See Support Portal for alternative products.



Data sheet

Feature	Value
Outside diameter	16 mm
Bending radius relevant for flow rate	60 mm
Inside diameter	9 mm
Min. bending radius	30 mm
Operating pressure complete temperature range	-0.95 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-20 ... 80 °C
Product weight according to length	0.186 kg/m
Pneumatic connection	für Stecktülle Innen-Ø 9 mm
Colour	blue
Shore hardness	A 68 +/- 5
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	NBR