

Silencer
U-1/2
Part number: 2310



Data sheet

Feature	Value
Mounting position	optional
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Flow rate to atmosphere	10300 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Sound pressure level	82 dB(A)
Ambient temperature	-10 °C...70 °C
Product weight	58.2 g
Pneumatic connection	G1/2
Material shock absorber insert	PE
Note on materials	RoHS-compliant