

Sealing ring
NPAS-C1-R-G38-P-FD-P10
Part number: 2652519

FESTO



Data sheet

Feature	Value
Size of pack	10
Mounting position	optional
Operating pressure complete temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) Water vapour
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B2-L
Suitable for use with food	See supplementary material information
Ambient temperature	-20 °C...120 °C
Nominal torque	35 Nm
Tolerance for nominal tightening torque	± 10%
Product weight	0.15 g
Pneumatic connection	G3/8
Note on materials	RoHS-compliant
Material seals	PEEK