

**Parallel kit**  
**EAMM-U-70-D32-52B/C-96**  
Part number: 2755890



**Data sheet**

| Feature                               | Value                 |
|---------------------------------------|-----------------------|
| Size                                  | 70                    |
| Mounting position                     | optional              |
| Gear unit ratio                       | 1:1                   |
| Max. rotational speed                 | 5000 rpm              |
| LABS (PWIS) conformity                | VDMA24364 zone III    |
| Storage temperature                   | -25 °C...60 °C        |
| Relative air humidity                 | 0 - 95%               |
| Degree of protection                  | IP40                  |
| Ambient temperature                   | -10 °C...60 °C        |
| Mass moment of inertia                | 118 kgmm <sup>2</sup> |
| Frictional torque independent of load | 0.18 Nm               |
| Transmittable torque                  | 7 Nm                  |
| Product weight                        | 1800 g                |
| Interface code, actuator              | D32B                  |
| Interface code, motor in              | 52B<br>52C            |
| Note on materials                     | RoHS-compliant        |