

# Clamping sleeve EAMH-86-9-C27.3

Part number: 2789221

FESTO



## Data sheet

| Feature                | Value                  |
|------------------------|------------------------|
| Size                   | 86                     |
| Mounting position      | optional               |
| Max. rotational speed  | 5000 rpm               |
| LABS (PWIS) conformity | VDMA24364-B2-L         |
| Storage temperature    | -25 °C...60 °C         |
| Relative air humidity  | 0 - 95%                |
| Ambient temperature    | -10 °C...60 °C         |
| Mass moment of inertia | 11.6 kgmm <sup>2</sup> |
| Product weight         | 116 g                  |
| Note on materials      | RoHS-compliant         |