

**Clamping sleeve**  
**EAMH-60-11-C18.1-P**  
Part number: 2789343



**Data sheet**

| Feature                | Value                  |
|------------------------|------------------------|
| Size                   | 60                     |
| Mounting position      | optional               |
| Max. rotational speed  | 6000 rpm               |
| LABS (PWIS) conformity | VDMA24364-B2-L         |
| Storage temperature    | -25 °C...60 °C         |
| Relative air humidity  | 0 - 95%                |
| Ambient temperature    | -10 °C...60 °C         |
| Mass moment of inertia | 1.31 kgmm <sup>2</sup> |
| Product weight         | 35 g                   |
| Note on materials      | RoHS-compliant         |