

Union nut
MCK-PK-9
Part number: 2967

FESTO



Data sheet

Feature	Value
Size	Female thread M16x1
Operating pressure complete temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Pneumatic connection, port 1	For barbed fitting inside diameter of 9 mm with union nut
Material union nut	Wrought aluminium alloy, anodised
Note on materials	RoHS-compliant