

Sub-base
VABS-S7-BE-B-G14-VDE1
Part number: 2999476

FESTO



Data sheet

Feature	Value
Mounting position	optional
Pilot air supply	Internal
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar
Flow rate Kv pressurisation	2.2 m³/h
Flow rate Kv exhaust	8.6 m³/h
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [---]
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Product weight	250 g
Type of mounting	With through-hole
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	VDI/VDE 3845 (NAMUR)
Pneumatic connection, port 3	G1/4
Note on materials	RoHS-compliant
Material sub-base	Ematal coated aluminium
Material seals	NBR