


Barbed fitting CRCN-M5-PK-2

Part number: 30985

FESTO



Data sheet

Feature	Value
Nominal size	1.5 mm
Type of seal on screwed plug	Sealing ring
Size of pack	10
Operating pressure complete temperature range	-0.95 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitable for use with food	See supplementary material information
Ambient temperature	0 °C...60 °C
Product weight	1.8 g
Pneumatic connection, port 1	Male thread M5
Pneumatic connection, port 2	For tubing outer diameter of 3 mm
Note on materials	RoHS-compliant
Material housing	High-alloy stainless steel
Material thread seal	NBR High-alloy stainless steel