

Clevis foot
LSNG-100
Part number: 31745



Data sheet

Feature	Value
Size	100
Based on standard	VDMA 24562
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...150 °C
Max. load capacity	9 kN
Product weight	1358 g
Note on materials	RoHS-compliant
Material mounting	Spheroidal graphite cast iron
Material rod end bearing	Steel PTFE