

Right angle clevis foot LQG-63

Part number: 31771

FESTO



Data sheet

Feature	Value
Size	63
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C...150 °C
Max. load capacity	4 kN
Product weight	784 g
	27.63 oz
Note on materials	RoHS-compliant
Material mounting	Spheroidal graphite cast iron
Material bolt	Case-hardened steel
Material lock	Spring steel