

Rod clevis SGA-M10X1,25

Part number: 32954

FESTO



Data sheet

Feature	Value
Size	M10x1.25
Radial deviation +/-	5 mm
Angle compensation +/-	120 deg
Mounting position	optional
Threaded connection	Male thread M10x1.25
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...150 °C
Max. load capacity	0.9 kN
Product weight	129 g
Note on materials	RoHS-compliant
Material bolt	Steel Galvanised
Material rod eye	Steel Galvanised
Material lock	Spring steel, galvanised