

Check valve
H-1/8-A/I
Part number: 3324

FESTO



Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Type of mounting	In-line installation
Standard nominal flow rate (standardised to DIN 1343)	280 l/min
Operating pressure	0.04 MPa...0.8 MPa 0.4 bar...8 bar
Ambient temperature	-10 °C...60 °C
Material housing	Brass
Operating medium	Compressed air to ISO 8573-1:2010 [7:...]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B2-L
Media temperature	-10 °C...60 °C
Product weight	21 g
Material seals	NBR