

Clevis foot
LNG-63
Part number: 33893



Data sheet

Feature	Value
Size	63
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...80 °C
Max. load capacity	4 kN
Product weight	486 g
Note on materials	RoHS-compliant
Material mounting	Spheroidal graphite cast iron
Material bearing	PA