


Pneumatic valve VLX-2-3/8-MS

Part number: 34433

FESTO



Data sheet

Feature	Value
Design	Diaphragm valve
Type of actuation	Pneumatic
Sealing principle	Soft
Mounting position	optional
Type of mounting	In-line installation
Connection Process valve	G3/8
Nominal size	13 mm
Valve function	2/2-way, closed, monostable
Flow direction	Non-reversible
Medium pressure	1 bar...10 bar
Exhaust-air function	Without flow control option
Type of reset	Pneumatic spring
Type of piloting	Pilot actuated
Pilot medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Medium	Filtered compressed air, grade of filtration 200 µm
Media temperature	-10 °C...80 °C
Ambient temperature	-10 °C...60 °C
Standard nominal flow rate (standardised to DIN 1343)	3800 l/min
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Material housing	Brass
Material screws	High-alloy stainless steel
Material number screw	1.4301
Product weight	470 g