

Suction cup complete VAS-30-1/8-NBR

Part number: 34587

FESTO



Data sheet

Feature	Value
Nominal size	3 mm
Suction cup diameter	30 mm
Effective suction diameter	25 mm
Position of connection	Top
Suction cup shape	Round, flat
Operating pressure	-0.095 MPa...0 MPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-0.07 MPa -0.7 bar -10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-20 °C...80 °C
Breakaway force at 70% vacuum	34 N
Holding force at nominal operating pressure	34 N
Mounting thread	G1/8
Suction cup mounting	G1/8
Vacuum connection	G1/8
Colour	Black
Shore hardness	70 +/- 5
Material screwed plug	Brass
Note on materials	RoHS-compliant
Material suction cup	NBR