

Low consumption air gun LSP-1/4-D

Part number: 35528

FESTO



Data sheet

Feature	Value
Exhaust-air function	Metered blowing
Operating pressure	0 bar...10 bar
Flow rate to atmosphere	120 l/min
Standard nominal flow rate (standardised to DIN 1343)	120 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Sound pressure level	90 dB(A)
Ambient temperature	-10 °C...50 °C
Product weight	240 g
Pneumatic connection	Female thread G1/4
Note on materials	RoHS-compliant
Material housing	Wrought aluminium alloy