

# Coupling piece KSZ-M8

Part number: 36124

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Size   | M8   |
| Mounting position                                  | optional   |
| Threaded connection                                | Female thread M8   |
| Corrosion resistance class CRC                     | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                             | VDMA24364-B2-L   |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper are excluded from use.<br>Exceptions are printed circuit boards, cables, electrical plug connectors and coils |
| Ambient temperature                                | -40 °C...150 °C  |
| Product weight                                     | 70 g   |
| Note on materials                                  | RoHS-compliant   |
| Material mounting                                  | Steel<br>Galvanised  |
| Material thread piece                              | Steel<br>Galvanised  |