


Bellows cylinder EB-215-155

Part number: 36492

FESTO



Data sheet

Feature	Value
Size	215
Required installation diameter	230 mm
Stroke	155 mm
Max. extended height	230 mm
Max. angle of inclination	30 deg
Max. offset	20 mm
Min. installation height	75 mm
Mode of operation	Single-acting
Operating pressure	0 bar...8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [:-:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C...70 °C
Reset force	200 N
Product weight	2300 g
Type of mounting	Via female thread
Pneumatic connection	G3/4
Note on materials	RoHS-compliant
Material bellows	NR/BR
Material housing	Steel Galvanised