

Quick coupling socket KD2-M5-A

Part number: 4087

FESTO



Data sheet

Feature	Value
Nominal size	2.4 mm
Operating pressure complete temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Standard nominal flow rate (standardised to DIN 1343)	83 l/min...131 l/min
Nominal flow rate standardised according to ISO 8778	90 l/min...142 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Nominal torque	0.85 Nm
Tolerance for nominal tightening torque	± 15%
Product weight	10 g
Pneumatic connection, port 1	Male thread M5
Note on materials	RoHS-compliant
Material seals	NBR
Material spring	High-alloy stainless steel
Material housing	Brass, nickel-plated
Material thread seal	NBR High-alloy stainless steel
Material thread piece	Nickel-plated brass
Material ball	High-alloy stainless steel
Material snap ring	High-alloy stainless steel
Valve body material	Brass
Material releasing sleeve	Nickel-plated brass