

**Counter bearing**  
**EAMG-U1-60-G2**  
Part number: 4164963



**Data sheet**

| Feature                | Value          |
|------------------------|----------------|
| Size                   | 60             |
| Mounting position      | optional       |
| Max. rotational speed  | 6000 rpm       |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature    | -25 °C...60 °C |
| Relative air humidity  | 0 - 95%        |
| Ambient temperature    | -10 °C...60 °C |
| Product weight         | 37 g           |
| Note on materials      | RoHS-compliant |