

# Pressure indicator OH-22-GN

Part number: 4237

FESTO



## Data sheet

Feature	Value
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...45 °C
Product weight	25 g
Pneumatic connection	G1/8
Note on materials	RoHS-compliant