

Ball valve
VZBM-3/8-RP-40-D-2-F03-B2B3
 Part number: 4405647

FESTO



Data sheet

Feature	Value
Design	2-way ball valve
Type of actuation	Mechanical
Sealing principle	Soft
Mounting position	optional
Type of mounting	In-line installation
Connection Process valve	Rp3/8
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F03
Inside diameter	10 mm
Nominal size DN	10
Valve function	2/2
Flow direction	Reversible
Nominal pressure PN	40
Breakaway torque at differential pressure, nominal pressure, process valve PN	3.2 Nm
Based on standard	EN 10226-1 ISO 5211
Medium	Compressed air to ISO 8573-1:2010 [-:::] Inert gases Water – no water vapour Neutral fluids
Media temperature	-20 °C...130 °C
Flow rate Kv	9.4 m³/h
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	Brass Nickel-plated
Material number housing	CW617N
Material seals	HNBR PTFE

Feature	Value
Material ball	Brass Chrome-plated
Material number ball	CW614N
Material shaft	Brass
Material number shaft	CW614N
Product weight	390 g
CE mark (see declaration of conformity)	In accordance with EU Pressure Equipment Directive
Corrosion resistance class CRC	1 - Low corrosion stress