

Parallel kit
EAMM-U-87-T46-87A-114
Part number: 4819278

FESTO



Data sheet

Feature	Value
Size	87
Centre-to-centre distance	114 mm
Mounting position	optional
Gear unit ratio	1:1
Max. rotational speed	3000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	0 °C...50 °C
Mass moment of inertia	41.2 kgmm ²
Frictional torque independent of load	0.22 Nm
Transmittable torque	3 Nm
Product weight	877 g
Interface code, actuator	T46
Interface code, motor in	87A
Note on materials	RoHS-compliant