


Stem actuated valve

V/O-3-1/8

Part number: 4938

FESTO



Data sheet

Feature	Value
Valve function	3/2-way, monostable, open/closed
Type of actuation	Mechanical
Standard nominal flow rate (standardised to DIN 1343)	140 l/min
pneumatic working port	G1/8
Operating pressure	-0.95 bar...8 bar
Design	Piston seat
Nominal size	3.5 mm
Type of piloting	Direct
Operating medium	Compressed air to ISO 8573-1:2010 [:-::-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Actuating force	28 N
Actuating force, normally closed	37.53 N
Product weight	90 g
Type of mounting	With through-hole
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Pneumatic connection, port 3	G1/8
Material seals	NBR
Material housing	Anodised aluminium