

Clevis foot LN-50

Part number: 5149

FESTO



Data sheet

Feature	Value
Size	50
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C...150 °C
Product weight	323 g
Note on materials	RoHS-compliant
Material mounting	Tempered steel