

Control element VAOH-P15-H13

Part number: 5196471

FESTO



Data sheet

Feature	Value
Stroke	20 mm
Piston diameter	50 mm
Mounting position	optional
Position detection	Via proximity switch
Operating pressure	1 bar
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Product weight	1350 g
Pneumatic connection, port 1	G1/8
Note on materials	RoHS-compliant