

Plastic tubing PUN-V0-6X1-WS

Part number: 525454

FESTO



Data sheet

Feature	Value
Outside diameter	6 mm
Flow-relevant bending radius	26.5 mm
Inside diameter	4 mm
Min. bending radius	12 mm
Tubing characteristics	Suitable for energy chains
Operating pressure complete temperature range	-0.095 MPa...0.7 MPa -0.95 bar...7 bar -13.775 psi...101.5 psi
Temperature-dependent operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Note on operating pressure	Water: max. 0.6 MPa at max. 50°C
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7:...] Water (liquid, ice-free)
Fire test material	UL94 V-0 (3 mm) UL94 V-2 (0.75 mm)
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C...60 °C
Note on ambient temperature	Unpressurised use up to 90 °C
Product weight according to length	0.02 kg/m
Pneumatic connection	For push-in connector O.D. 6 mm For barbed fitting I.D. 4 mm with union nut For barbed fitting I.D. 4 mm
Colour	White
Note to colour	Deviates from the standard colour due to flame protection
Shore hardness	D 54 +/-3
Note on materials	RoHS-compliant
Material tubing	TPE-U(PU)