


**Plastic tubing**  
**PAN-V0-12X1,5-BL**  
 Part number: 525469

**FESTO**



**Data sheet**

| Feature                                       | Value                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------|
| Outside diameter                              | 14 mm                                                                                |
| Outside diameter for push-in fitting          | 12 mm                                                                                |
| Flow-relevant bending radius                  | 65 mm                                                                                |
| Inside diameter                               | 9 mm                                                                                 |
| Min. bending radius                           | 43 mm                                                                                |
| Tubing characteristics                        | Suitable for energy chains                                                           |
| Operating pressure complete temperature range | -0.095 MPa...0.3 MPa<br>-0.95 bar...3 bar<br>-13.775 psi...43.5 psi                  |
| Temperature-dependent operating pressure      | -0.095 MPa...1.2 MPa<br>-0.95 bar...12 bar<br>-13.775 psi...174 psi                  |
| Note on operating pressure                    | Mineral oil: max. 0.3 MPa at max. 90 °C<br>Water: max. 0.3 MPa at max. 90 °C         |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7:-:-]<br>Mineral oil<br>Water (liquid, ice-free) |
| Fire test material                            | UL94 V-0 (casing)                                                                    |
| LABS (PWIS) conformity                        | VDMA24364-B2-L                                                                       |
| Ambient temperature                           | -30 °C...90 °C                                                                       |
| Product weight according to length            | 0.133 kg/m                                                                           |
| Pneumatic connection                          | For push-in connector outside diameter of 12 mm                                      |
| Colour                                        | Blue                                                                                 |
| Shore hardness                                | A 72 +/-4<br>D 57 +/-3                                                               |
| Note on materials                             | RoHS-compliant                                                                       |
| Material tubing                               | PA12-P<br>PVC-P                                                                      |