

Suction cup without connector ESV-40-BT

Part number: 526006

FESTO



Data sheet

Feature	Value
Height compensator for suction-cup holder	9 mm
Min. workpiece radius	35 mm
Suction cup diameter	40 mm
Suction cup volume	9.8 cm ³
Mounting position	optional
Design	Bellows
Suction cup shape	Round bellows 1.5 convolutions
Operating pressure	-0.95 bar...0 bar
Nominal operating pressure	-0.7 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...80 °C
Breakaway force at 70% vacuum	59 N
Holding force at nominal operating pressure	59 N
Lateral force at nominal operating pressure	22 N
Product weight	10.5 g
Type of mounting	Via vacuum port
Colour	Red-brown
Shore hardness	72 +/- 5
Note on materials	RoHS-compliant
Material suction cup	Vulkollan