

**LOE-M7-D-MICRO**

Lubricator

Data sheet

Part no.: 526312

Page:1

<b>Feature</b>	<b>Data/description</b>
Design lubricator	<b>Direct proportional</b>
Modular design	<b>Yes</b>
Input pressure 1 max. (bar)	<b>10 bar</b>
Air connection type 1	<b>Female thread</b>
Thread for port 1	<b>M7</b>
Air connection type 2	<b>Female thread</b>
Thread for port 2	<b>M7</b>
Installation position	<b>vertical</b>
Type of mounting	<b>In-line/bracket</b>
Minimum ambient temperature	<b>-10 °C</b>
Maximum ambient temperature	<b>60 °C</b>
Minimum medium temperature	<b>-10 °C</b>
Maximum medium temperature	<b>60 °C</b>
Minimum flow for lubricator operation	<b>3 l/min</b>
Oil capacity max.	<b>6,5 cm<sup>3</sup></b>
Metal bowl guard	<b>No</b>
Material of housing	<b>AL, die-cast metal</b>
Material of bowl	<b>PC</b>
Product weight	<b>0,059 kg</b>
Standard nominal flow rate 1-2	<b>380 l/min</b>
Operating medium input 1	<b>Compressed air, filtered 5 µm, unlubricated</b>
Operating medium output 2	<b>Compressed air, filtered 5 µm, lubricated</b>