



Branching module MS6-FRM-1/4-Z

Part number: 529860

FESTO

Direction of flow: from right to left.



Data sheet

Feature	Value
Assembly position	Any
Design structure	Branching module
Operating pressure	0 ... 20 bar
Standard nominal flow rate in main flow direction 1->2	4,200 l/min
Standard nominal flow rate outlet at top	6,000 l/min
Standard nominal flow rate outlet at bottom	6,400 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	458 g
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Pneumatic connection, port 3	G1/2
Pneumatic connection, port 4	G1/2
Materials note	Conforms to RoHS
Materials information, housing	Aluminium die cast