

Coupling
EAMC-B-15-22-5-5
Part number: 530085



Data sheet

Feature	Value
Mounting diameter 1	5 mm
Mounting diameter 2	5 mm
Size	15
Nominal length	22 mm
Mounting position	optional
Max. rotational speed	12000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	0.13 kgmm ²
Transmittable torque	1 Nm
Product weight	6 g
Note on materials	RoHS-compliant