

Quick coupling plug KS4-1/4-A-R

Part number: 531677

FESTO



Data sheet

Feature	Value
Nominal size	8 mm
Operating pressure complete temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Standard nominal flow rate (standardised to DIN 1343)	765 l/min
Nominal flow rate standardised according to ISO 8778	829.3 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Nominal torque	9.5 Nm
Tolerance for nominal tightening torque	± 15%
Product weight	46 g
Pneumatic connection, port 1	Male thread G1/4
Note on materials	RoHS-compliant
Material seals	NBR
Material spring	High-alloy stainless steel
Material thread seal	PA66-GF30/TPE-U
Information on materials	Brass
Valve body material	Brass