


# Lubricator MS4N-LOE-1/8-R-Z

Part number: 531705

FESTO

Plastic bowl with plastic bowl guard, direction of flow: from right to left.



## Data sheet

Feature	Value
Size	4
Series	MS
Assembly position	Vertical +/- 5°
Design structure	proportional standard mist lubricator
Max. oil capacity	30 ml
Bowl guard	Plastic guard
Inlet pressure 1	1 ... 12 bar
Minimum flow rate for lubricator function	40 l/min
Standard nominal flow rate	1,100 l/min
Operating medium	Compressed air
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Medium temperature	-10 ... 60 °C
Oil viscosity	ISO VG 32
Ambient temperature	-10 ... 60 °C
Product weight	194 g
Mounting type	with accessories Optional Line installation
Pneumatic connection, port 1	NPT1/8-27
Pneumatic connection, port 2	NPT1/8-27
Materials information, housing	Aluminium die cast
Materials information for bowl	PC