

Spiral plastic tubing
PUN-10X1,5-SG-2,4-BL-1/4
Part number: 533463

FESTO



Data sheet

Feature	Value
Working length	2.4 m
Outside diameter	9.5 mm
Block length	0.889 m
Flow-relevant bending radius	50 mm
Inside diameter	6.4 mm
Winding diameter	42 mm
Number of turns	21
Temperature-dependent operating pressure	-0.95 bar...15 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C...60 °C
Nominal torque	11 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	180 g
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	Male thread G1/4
Colour	Blue
Shore hardness	A 87 +/- 3
Material connecting thread	Brass Nickel-plated
Material buckling protection	POM
Material tubing	TPE-U(PU)