

**Spiral plastic tubing**  
**PUN-10X1,5-SG-6-BL-1/4**  
Part number: 533465

**FESTO**



**Data sheet**

| Feature                                  | Value                                     |
|------------------------------------------|-------------------------------------------|
| Working length                           | 6 m                                       |
| Outside diameter                         | 9.5 mm                                    |
| Block length                             | 1.317 m                                   |
| Flow-relevant bending radius             | 50 mm                                     |
| Inside diameter                          | 6.4 mm                                    |
| Winding diameter                         | 42 mm                                     |
| Number of turns                          | 66                                        |
| Temperature-dependent operating pressure | -0.95 bar...15 bar                        |
| Operating medium                         | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Corrosion resistance class CRC           | 1 - Low corrosion stress                  |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L                         |
| Ambient temperature                      | -40 °C...60 °C                            |
| Nominal torque                           | 11 Nm                                     |
| Tolerance for nominal tightening torque  | ± 20%                                     |
| Product weight                           | 430 g                                     |
| Pneumatic connection, port 1             | Male thread G1/4                          |
| Pneumatic connection, port 2             | Male thread G1/4                          |
| Colour                                   | Blue                                      |
| Shore hardness                           | A 87 +/- 3                                |
| Material connecting thread               | Brass<br>Nickel-plated                    |
| Material buckling protection             | POM                                       |
| Material tubing                          | TPE-U(PU)                                 |