

**Coupling**  
**EAMC-30-32-6-8**  
Part number: 533708



**Data sheet**

| Feature                | Value                  |
|------------------------|------------------------|
| Mounting diameter 1    | 6 mm                   |
| Mounting diameter 2    | 8 mm                   |
| Size                   | 30                     |
| Nominal length         | 32 mm                  |
| Mounting position      | optional               |
| Max. rotational speed  | 8000 rpm               |
| LABS (PWIS) conformity | VDMA24364-B2-L         |
| Storage temperature    | -25 °C...60 °C         |
| Relative air humidity  | 0 - 95%                |
| Ambient temperature    | -25 °C...60 °C         |
| Mass moment of inertia | 5.87 kgmm <sup>2</sup> |
| Transmittable torque   | 6.5 Nm                 |
| Product weight         | 48 g                   |
| Note on materials      | RoHS-compliant         |