

# Sub-base-SET MS12-AGH

Part number: 537137

FESTO



## Data sheet

| Feature                        | Value                                     |
|--------------------------------|-------------------------------------------|
| Size                           | 12                                        |
| Series                         | MS                                        |
| Mounting position              | optional                                  |
| Operating medium               | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress             |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L                         |
| Storage temperature            | -10 °C...60 °C                            |
| Media temperature              | -10 °C...60 °C                            |
| Product weight                 | 1300 g                                    |
| Pneumatic connection, port 1   | G1 1/2                                    |
| Pneumatic connection, port 2   | G1 1/2                                    |
| Note on materials              | RoHS-compliant                            |
| Material sub-base              | Die-cast aluminium                        |
| Material seals                 | NBR                                       |