

# blanking plug QSPC18

Part number: 537533

FESTO

To seal connections on valves or blanking plates.



## Data sheet

Feature	Value
Assembly position	Any
Container size	10
Operating pressure complete temperature range	0.9 ... 8 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Medium temperature	-5 ... 50 °C
Ambient temperature	-5 ... 50 °C
Product weight	5 g
Pneumatic connection, port 1	Cartridge 18 mm
Materials note	Free of copper and PTFE Conforms to RoHS
Material information, blanking plug	Reinforced PA
Material information, separator element	Steel
Information on materials, O-ring	NBR