

Plastic tubing PUN-E-10x1,25-SW

Part number: 538468

FESTO

Suitable for use with QS push-in connectors, highly flexible, hydrolysis resistant, micron stable, approved for use in food processing.

Type to be discontinued. Available until 2012.



Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	60 mm
Inside diameter	7.5 mm
Min. bending radius	26 mm
Temperature dependent operating pressure	-0.95 ... 8 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Food-industry approval	FDA 2002/72/EG
Ambient temperature	-35 ... 50 °C
Product weight according to length	0.044 kg/m
Colour	Black
Shore hardness	D 52 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	TPE-U(PU)