

Plug socket
NTSD-GD-9-M12-5POL-RK
Part number: 538999



Data sheet

Feature	Value
Electrical connection	5-pin Straight plug connector/screw terminal
Permissible current load	3 A
Permissible cable diameter	6 mm...8 mm
Connection cross section	0.75 mm ²
Degree of protection	IP67
Ambient temperature	-40 °C...85 °C
Note on materials	RoHS-compliant
Material housing	PA
Housing colour	Black