

Plug socket MSSD-EB-M12

Part number: 539712

FESTO



Data sheet

Feature	Value
Frequency of connection	50
Type of mounting	On solenoid valve via M2.5 central screw
Mounting position	optional
Product weight	11 g
Electrical connection	3-pin Angled socket Type C To DIN EN 175301-803 Square design
Cable fitting	M12
Permissible cable diameter	4 mm...6 mm
Connection cross section	1.5 mm ²
Degree of protection	IP65 To IEC 60529
Ambient temperature	-40 °C...125 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	PA-reinforced
Material seals	HNBR