

On/off valve MS6N-EM1

Part number: 541301

FESTO



Data sheet

| Feature | Value |
|---|--|
| Design | Rotary gate valve |
| Type of actuation | Manual |
| Exhaust-air function | Without flow control option |
| Type of piloting | Direct |
| Valve function | 3/2 bistable |
| Operating pressure | 0 bar...18 bar |
| Standard nominal flow rate (standardised to DIN 1343) | 3000 l/min...8700 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| Note on materials | RoHS-compliant |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Media temperature | -10 °C...60 °C |
| Ambient temperature | -10 °C...60 °C |
| Approval | c UL us - Recognized (OL) |
| Suitable for use with food | See supplementary material information |
| Type of mounting | Either: In-line installation With accessories |
| Mounting position | optional |
| Flow direction | Non-reversible |
| Pneumatic connection, port 3 | 1/2 NPT |
| Material seals | TPE-U(PU) |
| Material housing | Die-cast aluminium |